

INSTALLATION INSTRUCTIONS

SERIES 6600 BEDPAN FLUSHER / SANITIZER

Specifications

Series 6600 Bedpan Flusher / Sanitizer

Height 1470 mm

Width 650 mm

Depth (closed) 515 mm

Depth (open) 835 mm

Installation

Both Hot and Cold stopcocks should be situated above or next to the machine either to the left or right and in an accessible position.

Service Requirements

A Cold Water, 15mmBSP, 100 kPa min

B Chimney Vent, 50mm BSP, to outside atmosphere

C Hot Water, 15mm BSP, 50 kPa min, 60°C min

D Sewer, 100mm, S or P outlet

E Electrical, 415V, 16kW 50Hz

F Hot Water tank overflow, 50mm

